


Internal Flexibox

Prysmian Part Numbers: See Below



The Internal Flexibox is a wall box designed for internal use with 8 splice trays and up to 8 individual inputs for up to 24 cables. Each splice tray is able to accommodate 12 fibre splices and the box has a tube storage area. The Flexibox is available with a lock for security and also has a removable cover for extra access whilst splicing and routing fibres. The box has been designed to stack multiple Flexiboxes side-by-side, without compromising space.

Features and Benefits

- Capacity for up to 96 fusion splices
- Suitable for up to 24 input cables, enterable from the top and bottom of the box
- The cable entries are suitable for
 - 1 x cable from 5 to 12 mm in diameter
 - 2 x cables from 5 to 6.5mm in diameter
 - 3 x cables from 2.5 to 4.5mm in diameter
- Up to 12 fusion splices can be accommodated into each of the splice trays.
- Can accommodate optical splitters. Contact Prysmian for further details.
- Easily installed and fitted to the wall or inside a riser.
- Suitable for internal use only and manufactured from UL94-V0 rated material.
- Input and output cables are retained using CSM/Aramid

Kit Contents

- The Flexibox is supplied with a base, cover, 8 splice trays, 1 manifold & cover, 2 x strength member retention posts, 4 x wall fixing kits and 3 cable entries.
- **Note** Splice protectors are not supplied and must be ordered separately. Extra cable entry kits must also be ordered separately.

Additional Items

- Cable entry kits (See below)
- Splice Protectors

Part Numbers

- **XCPSC03687** – 8 trays, 3 cable entry glands (1 6-12mm, 2 x 4-6mm), security lock

Technical Data

- No of Splice Trays: 8
- Max capacity (fibres) 96
- Max diameter of input cable: 12mm
- Max no. of inputs: 24
- Required space envelope (mm): (h) 345 x (w) 272 x (d) 105
- Operating temperature: -20°C to + 60°C (5 to 95% RH)*
- Material: FR ABS
- Colour: White RAL 9016
- Flammability rating: UL94-V0

* To be confirmed

Logistics

- Packing Dimensions (mm): (h) 420
(w) 315
(d) 135
- Packed Weight (kg): TBC
- Net weight (kg): TBC

Additional Items

Cable Entries

Cable entries are used for bringing cables in to the box. The cable entries come in multiple configurations as below:

- Prysmian Part No. – XKTSC02471 (Single way 6-12mm)**
- XKTSC02335 (Single way 5-9mm)**
- XKTSC02542 (Dual way 4-6mm)**
- XXXXXXXXXXXX (3 way 2.5-4.5mm)**



Heat Shrink Splice Protectors

Splice protectors are used to protect the fibre splice. They are 2.2mm in diameter and 40mm in length.

- Prysmian Part No. – XKTSC00050 (pack of 12)**
- XPESC00053 (pack of 50)**



Please contact your local sales office listed on www.prysmiangroup.com

© Prysmian Group 2020, All Rights Reserved.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed correct at the time of issue. Prysmian Group reserves the right to amend this specification without notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.