



# Properties of cabled Non-zero Dispersion-shifted SM fibre

# Non-zero dispersion-shifted single mode fibre G.655

#### **General and application**

The optical fibres are made of a high grade doped silica core surrounded by a silica cladding; they are coated with a dual layer of UV cured acrylate based coating.

This single mode fibre supports high-power signals and longer distances, as well as closely spaced DWDM (dense WDM) channels at rates of 10 Gb/s or higher (40 Gb/s). With larger Effective Area the fibre is capable to operate between the Conventional Band (1530 to 1565 nm) and in the Extended or Large Band (1565 to 1625 nm). Fibre is suitable to support the highest bit-rate transmission currently used in optical communication systems and due to its particular features will also support future system upgrades.

It is optimized for WDM and long-distance cable runs such as transoceanic cables.

#### **Standards and Norms**

YEO (0700 0 F0 O )	TOO / TEO 44004   1 TOO / TEO 04700
IEC 60793-2-50 Category B4	ISO / IEC 11801 and ISO / IEC 24702
ITU-T Recommendation G.655 (all tables)	AS / NZS 3080

#### Attenuation of cabled fibre

<u>Attribute</u>	Measurement method	<u>Units</u>	<u>Limits</u>
Maximum attenuation value of cable @ 1550 nm	IEC 60793-1-40	dB/km	0.23 / 0.21 (average)
Maximum attenuation value of cable @ 1625 nm		dB/km	0.25/ 0.23 (average)

#### **Group index of refraction**

<u>Attribute</u>	Measurement method	<u>Value</u>
Effective group index at 1550 nm and 1625 nm	IEC 60793-1-22	1.468

## **Optical properties**

<u>nits</u>
± 0.4
÷ 6.0
÷ 11.2
72
450*
0.1
0.04
÷ 7 14

<sup>\*</sup> guaranteed value according to the ITU-T (ATM G650) method

# **Geometrical properties**

<u>Attribute</u>	Measurement method	<u>Units</u>	<u>Limits</u>
Cladding diameter		μm	$125 \pm 0.7$
Cladding non-circularity	IEC 60793-1-20	%	≤ 1.0
Core (MFD) - dadding concentricity error		μm	≤ 0.5
Primary coating diameter		μm	$245 \pm 5$
Primary coating – cladding concentricity error	IEC 60793-1-21	μm	≤10
Primary coating non-circularity		μm	≤6

# NZDS\_G.655





## **Macrobending loss**

<u>Attribute</u>	Measurement method	<u>Units</u>	<u>Limits</u>
100 turns on a R= 30 mm mandrel @ 1550 nm/1625 nm	IEC 60793-1-47	dB	≤ 0.05
1 tum on a R= 16 mm mandrel @ 1550 nm/1625 nm		dB	≤ 0.5

#### **Mechanical properties**

Attribute	Measurement method	<u>Units</u>	<u>Limits</u>
Proof stress level	IEC 60793-1-30	Gpa	≥ 0.7 (1% strain)
Fibre curl radius	IEC 60793-1-34	m	> 4
Strip force (peak)	IEC 60793-1-32	N	$1.2 \le F_{peak strip} \le 8.9$
Dynamic fatigue resistance aged and unaged	IEC 60793-1-33	$N_d$	≥ 20
Static fatigue resistance		$N_S$	≥ 23

All measurements in accordance with ITU-T G650 recommendations

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of PrysmianGroup. The information is believed to be correct at the time of issue. PrysmianGroup reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by PrysmianGroup.

<sup>©</sup> PrysmianGroup 2012, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by PrysmianGroup: any modification or alteration afterwards of product may give different result.