

Unexpected performance.

Our new Flat Xtra™ Cables – pure magic.





Flat Xtra™ cables do the trick.

Why lay a separate earth cable when you can do the job with only one flat cable? The new Flat Xtra™ allows you to cover up to 70%* longer runs in comparison to the standard design. All possible because we made the earth and cores the same size.

This means significant savings on labour and cable wastage. Available in 4 mm² and 6 mm².

Up to 3% cost savings*

On cable costs only. Non-inclusive of labour cost-savings for laying just one cable instead of two.

Up to 70% longer runs*

When comparing the maximum route length of our Flat Xtra against the standard TPS cable.

MAXIMUM RUN LENGTH BY CONDUCTOR SIZE

Conductor size		Protective	Circuit Breaker			Fuere
Active	Earth mm²	Device Rating (Amps)	Туре В	Type C	Type D	Fuses
mm²			Maximum route length, L _{max} (m)			
4	2.5	25	126	67	40	90
4	4	25	164	87	52	117
4	2.5	32	98	52	31	70
4	4	32	128	68	41	91
6	2.5	40	90	48	29	60
6	6	40	153	82	49	102

For circuit breakers the mean tripping currents are as follows;

Type B 4 times rated current Type C 7.5 times rated current Type D 12.5 times rated current

Fuses based on AS/NZS 60269.1 also known as BS 88 type fuses.

Table based on AS/NZS 3000. Nominal Phase voltage, 230V.

For a nominal phase voltage of not 230V, the maximum length may be determined by multiplying by a factor of U₀/230.

Suitable for use in commercial and industrial buildings. Will provide longer runs only where typical cable construction is limited by earth fault loop impedance.

* Conditions apply.

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.



Prysmian Australia Pty Ltd

Theathcote Road, Liverpool 2170 NSW, Australia Ph: 1300 300 304 Fx: 1300 300 307 E-mail: sales.au@prysmiangroup.com



